



Feboclean Bio-3

Low-VOC Wash for Ink Rollers and Blankets

Uses

Washing agent for cleaning printing blankets, rollers and printing plates. It is suitable for both manual cleaning and for use in automatic installations.

Feboclean BIO-3 is not meant to wash roller coverings that are solely used for UV printing (EPDM roller coverings).

Characteristics

- Flash point >180° C (>355° F)
- Water miscible
- Contains corrosion inhibitor
- Leaves no residue, rinse with water
- Slow evaporation
- Manufactured from renewable, vegetable based, raw materials
- Zero VOC, USEPA Method 24
- Meets the requirements of California SCAQMD Rule 1171
- Designated as a "Clean Air Solvent" by SCAQMD, Rule 1171
- <5.0 gm/L VOC, Rule 1171, Method 313

Application

Follow the automatic washing systems manufacturers' operating instructions. If manual cleaning with a hand rag, wear protective gloves during application. Follow all press safety procedures. Feboclean Bio-3 is used undiluted when manual cleaning. Rinse with water or water treated with BöttcherPro Aqualux.

Approvals

Feboclean BIO-3 is approved by the manufacturers Heidelberg, MAN, KBA, Baldwin and WIFAG for use in their machines.

Marking

Feboclean BIO-3 is classified and marked according to EC-Directive 88/379/EEC - in its latest version. It is not classified as a dangerous good in the sense of national and international transport regulations (GGVSE - ADR/RID - GGV See/IMDG).